

[See all 22 Products in Family](#)

**TECHSPEC® 25.4mm Dia. Precision Broadband Laser Mirror Substrate**



TECHSPEC® Laser Mirror Substrates

Stock #75-410 **NEW** 1 In Stock

⊖ 1 ⊕ £84.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£84.00 each
Qty 6-25	£74.00 each
Qty 26+	£65.20 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Laser Mirror Substrate **Type:**

**Physical & Mechanical Properties**

<3 **Parallelism (arcmin):**

**Clear Aperture (%):**

---

Ground **Back Surface:**

25.40 +0.0/-0.1 **Diameter (mm):**

---

8.00 ±0.2 **Thickness (mm):**

Ground, protective bevel as needed **Edges:**

## Optical Properties

10-5 **Surface Quality:**

λ/20 **Surface Flatness (P-V):**

---

Uncoated **Coating:**

[Fused Silica](#) (Corning 7980) **Substrate:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

---

## Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
- High Quality Fused Silica Substrates
- Imperial Sizes with Circular or Rectangular Geometries
- [Window Substrates](#) Also Available

TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.