

## 254mm Length, M4 and M6, Steel Post



Stock #72-769 NEW 14 In Stock

-

1

+

£9<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | £9.20 each                    |
| Need More?     | <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

|        |       |
|--------|-------|
|        | Type: |
| Metric |       |

Physical & Mechanical Properties

|       |                    |
|-------|--------------------|
|       | Diameter (mm):     |
| 12.7  |                    |
|       | Diameter (inches): |
| 0.5   |                    |
|       | Length (mm):       |
| 254.0 |                    |

|                                       |                  |
|---------------------------------------|------------------|
| 10                                    | Length (inches): |
| Threading & Mounting                  |                  |
| Thread 1: M4 x0.7<br>Thread 2: M6 x 1 | Male Thread:     |

|                           |                             |
|---------------------------|-----------------------------|
| Regulatory Compliance     |                             |
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 247:                  |

## Product Details

- English or Metric Versions Options Available
- Wide Variety of Lengths Available from 25.4 to 304.8mm (1" to 12").
- Removable Top and Bottom Set Screws Available

Stainless Steel Optical Mounting Posts are a practical and straightforward way to integrate optical assemblies and photonic equipment onto an [optical lab table](#) or [breadboard](#). All mounting posts are 12.7 mm (0.5") in diameter and are offered in various lengths from 25.4 to 304.8mm (1" to 12"). Each mounting post features a female thread on each end with a set screw preinstalled, making it simple to mount components with counterbore or tapped hole mounting features. Stainless Steel Optical Mounting Posts can be used with [Post Holders](#) to allow for height adjustment of the optical component, and for a secure connection with the optical benchtop. Thread values (M4 x0.7/M6 x 1.0 for Metric; 8-32/1/4-20 for English) are laser-engraved on the ends of each post for quick identification and integration.

**Note:** All posts have a through-hole that allows an Allen wrench, 5.5mm or 7/32" key size, or other tools to rotate the post easily.