

TECHSPEC<sup>®</sup> 25mm 266nm, Laser Line  $\lambda$ /20 High Tolerance Right Angle Mirror



Stock **#37-645** 2 In Stock

-

1

+

£268<sup>.80</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £268.80 each                  |
| Qty 6-25       | £223.20 each                  |
| Qty 26-49      | £214.40 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Right Angle Mirror

Physical & Mechanical Properties

Bevel:

Protective as needed

Clear Aperture (%):

90

|             |                             |
|-------------|-----------------------------|
| +0.00/-0.10 | Dimensional Tolerance (mm): |
| 35.40       | Length of Hypotenuse (mm):  |
| 25.00       | Length of Legs (mm):        |

Optical Properties

|                                                                                                                        |                                                       |
|------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------------|
| Laser Mirror (266nm)                                                                                                   | Coating:                                              |
| $\lambda/20$                                                                                                           | Surface Flatness (P-V):                               |
| 266                                                                                                                    | Design Wavelength DWL (nm):                           |
| <a href="#">Fused Silica</a> (Corning 7980)                                                                            | Substrate: <input type="checkbox"/>                   |
| Coating Specification:<br>R <sub>abs</sub> >99.5% @ 266nm @ 45° AOI<br>R <sub>avg</sub> >99.5% @ 263 - 268nm @ 45° AOI |                                                       |
| 20-10                                                                                                                  | Surface Quality:                                      |
| 1MW/cm <sup>2</sup> @ 266nm                                                                                            | Damage Threshold, Reference: <input type="checkbox"/> |
| ±1                                                                                                                     | Pyramid Tolerance (arcmin):                           |
| ±15                                                                                                                    | Angle Tolerance (arcsec):                             |

Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">Compliant</a> | Reach 209:                  |
| <a href="#">View</a>      | Certificate of Conformance: |

## Product Details

- >99.5% Reflectivity at the Design Wavelength
- ±15 Arcsecond Angular Tolerance
- High Thermal Stability Substrates

TECHSPEC® Laser Line  $\lambda/20$  High Tolerance Right Angle Mirrors are designed at Nd:YAG wavelengths with durable, high reflectivity dielectric coatings. Right angle mirrors are easily mounted and integrated into systems that redirect light 90°. With ±15 arcsecond angular tolerance and ±1 arcminute pyramid tolerance, these laser line mirrors simplify alignment when mounting. TECHSPEC® Laser Line  $\lambda/20$  High Tolerance Right Angle Mirrors feature laser induced damage threshold specifications making them ideal for demanding laser applications.



## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).