

TECHSPEC[®] 2.5mm Dia. x 2.0mm FL, VIS-NIR Coated, Plano-Convex Lens



Stock **#65-300** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£66.30

ADD TO CART

Qty 1-9
£66.30
Qty 10+
£59.71
Volume Pricing
Request Quote

ⓘ

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
2.50 +0.0/-0.025

Effective Focal Length EFL (mm):

2.00 @ 587.6nm
Back Focal Length BFL (mm): 1.57
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ N-LASF9
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.25
Radius R₁ (mm): 1.70
Clear Aperture CA (mm): 2
f/#: 0.8
Numerical Aperture NA: 0.63
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 1000
Damage Threshold, By Design: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant