

25.4mm Dia. x 25.4mm FL, 8 - 12µm BBAR Coated, ISP Optics Zinc Selenide (ZnSe) Meniscus Lens | AR812-ZC-PM-25-25

See More by [ISP Optics](#)



Stock **#24-932** 3-4 DAYS

-

1

+

£467.50

ADD TO CART

Qty 1+

£467.50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.13

Effective Focal Length EFL (mm):
25.40 @ 10.6µm

Substrate: Zinc Selenide (ZnSe), CVD Grade
f#: 1.00
Numerical Aperture NA: 0.50
Coating: BBAR (8000-12000nm)
Type: Meniscus Lens
Wavelength Range (nm): 8000 - 12000
Center Thickness CT (mm): 4.40 ±0.20
Centering (arcmin): <3
Clear Aperture (%): 90
Clear Aperture CA (mm): 22.86
Coating Specification: Ravg <0.5% @ 8 - 12µm Rabs <1% @ 8 - 12µm
Edge Thickness ET (mm): 2.00
Focal Length Tolerance (%): ±2
Model Number: AR812-ZC-PM-25-25
Radius R₁ (mm): 58.34
Radius R₂ (mm): 22.91
Surface Quality: 60-40
Irregularity (P-V) @ 10.6µm: λ/20

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View