

[See all 3 Products in Family](#)

TECHSPEC® 25.4mm Protected Silver $\lambda/10$ Knife-Edge Pickoff Mirror



25.4mm Enhanced Protected Silver $\lambda/10$ D-Shaped Pickoff Mirror, #36-137

Stock **#36-137** **4 In Stock**

⊖ 1 ⊕ £81⁰⁰

ADD TO CART

Volume Pricing

Qty 1-5	£81.60 each
Qty 6-25	£72.80 each
Qty 26+	£65.20 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Flat Mirror **Type:**

Physical & Mechanical Properties

25.40 **Diameter (mm):**

Back Surface:

Fine Grind	
+0.0/-0.20	Dimensional Tolerance (mm):
Protective as needed	Bevel:
Ground	Edges:
2	Parallelism (arcmin):
6.35 ±0.20	Thickness (mm):

Optical Properties

λ/10	Surface Flatness (P-V):
Fused Silica (Corning 7980)	Substrate: <input type="checkbox"/>
20-10	Surface Quality:
R _{avg} >98% @ 450 - 800nm R _{avg} >98.5% @ 2000 - 10,000nm	Coating Specification:
Protected Silver (450-10000nm)	Coating:
Metal	Coating Type:
450 - 10000	Wavelength Range (nm):
0.5 J/cm ² @ 532nm & 1064nm, 10ns	Damage Threshold, Reference: <input type="checkbox"/>

Regulatory Compliance


Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Designed to Separate Two Beams Propagating Closely Next to Each Other
- 45° Bevel
- Coating Aperture Up to the Knife-Edge
- Enhanced Aluminum, Protected Gold and Protected Silver Coating Options

Knife-Edge Pickoff Mirrors are designed to selectively reflect an individual beam from a group of tightly spaced beams, while minimizing the overall footprint of the application. These mirrors feature a sharp 45° bevel with a reflective coating that extends to the beveled edge on a precision Fused Silica substrate with λ/10 flatness to the bevel. Knife-Edge Pickoff Mirrors are ideal for applications that incorporate dispersion prisms and diffraction gratings. These mirrors are available in three metallic coating options with performance from the visible spectrum into the far IR.

Technical Information



Coating Curves

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

;