

[See all 5 Products in Family](#)

## 254mm FL, 1064nm Edmund Optics® F-Theta Lens



Stock #15-182 CLEARANCE [CONTACT US](#)

⊖ 1 ⊕ £685.<sup>56</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£685.56 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

F-Theta Lens **Type:**

### Physical & Mechanical Properties

122 **Maximum Diameter (mm):**

360.6 **Flange Distance (mm):**

20 **Input Beam Diameter, 1/e<sup>2</sup> (mm):**

76.0 **Maximum Length (mm):**

## Optical Properties

254.00 **Focal Length FL (mm):**

±25.00 **Scan Angle (°):**

157.0 x 157.0 **Scan Field (mm):**

Not Specified **Telecentricity (°):**

≥95 **Transmission (%):**

304.6 **Working Distance (mm):**

1064 **Design Wavelength DWL (nm):**

1064 **Wavelength Range (nm):**

25 **Focus Size Diameter, 1/e<sup>2</sup> (μm):**

## Threading & Mounting

M85 x 1.0 **Mounting Threads:**

## Regulatory Compliance

[View](#) **Certificate of Conformance:**

## Product Details

- Ideal for Laser Scanning Applications
- Diffraction Limited Across the Scan Field with Low Wavefront Error
- Long Working Distances and Large Scan Areas
- [Galvanometers](#), [Beam Expanders](#), and [Laser Sources](#) Also Available

Edmund Optics® F-Theta Lenses are designed to provide flat fields at the image plane of scanning systems and are used in conjunction with [galvanometers](#), [beam expanders](#), and [laser sources](#). These F-Theta Lenses feature compact form factors, offer a wide range of focal lengths up to 273mm, and large scan fields up to 164mm (X) x 164mm (Y). Optimized for common fiber laser sources and Nd:YAG fundamental or second harmonic, these lenses are available in design wavelengths of 532nm and 1064nm with common mounting threads for easy integration into galvo systems. Edmund Optics® F-Theta Lenses are a cost-effective solution for laser scanning and laser processing applications including laser marking, engraving, cutting, drilling, and 3D modeling.