

[See all 44 Products in Family](#)

TECHSPEC®

25.4mm x -50mm FL, VIS 0° Imaging Grade PCV Cylinder Lens



TECHSPEC® Beam Shaping PCV Cylinder Lenses

Stock **#34-663** 1 In Stock

-

1

+

£102<sup>00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £102.00 each                  |
| Qty 6-25       | £92.00 each                   |
| Qty 26-49      | £88.00 each                   |
| Need More?     | <a href="#">Request Quote</a> |

**i** Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Cylinder Lens, Plano-Concave

Type:

Physical & Mechanical Properties

25.40 +0.0/-0.025

Diameter (mm):

Bevel:

|                                      |                                  |
|--------------------------------------|----------------------------------|
| Protective as needed                 |                                  |
| 3.00                                 | Center Thickness CT (mm):        |
| ±0.1                                 | Center Thickness Tolerance (mm): |
| 22.86                                | Clear Aperture CA (mm):          |
| 6.23                                 | Edge Thickness ET (mm):          |
| Optical Properties                   |                                  |
| -50.00                               | Effective Focal Length EFL (mm): |
| N-BK7                                | Substrate: <input type="text"/>  |
| 2                                    | f/#:                             |
| 0.25                                 | Numerical Aperture NA:           |
| VIS 0° (425-675nm)                   | Coating:                         |
| 425 - 675                            | Wavelength Range (nm):           |
| -51.98                               | Back Focal Length BFL (mm):      |
| R <sub>avg</sub> ≤0.4% @ 425 - 675nm | Coating Specification:           |
| 25.84                                | Radius R <sub>1</sub> (mm):      |
| 40-20                                | Surface Quality:                 |
| 1.5λ                                 | Power (P-V) @ 632.8nm:           |
| λ/4                                  | Irregularity (P-V) @ 632.8nm:    |
| <5                                   | Plano Axis Wedge (arcmin):       |
| <5                                   | Power Axis Wedge (arcmin):       |
| Regulatory Compliance                |                                  |
| Compliant                            | RoHS 2015:                       |
| View                                 | Certificate of Conformance:      |
| Compliant                            | Reach 235:                       |

## Product Details

- Beam Shaping Grade Specifications
- Used with [TECHSPEC® Imaging Grade PCX Cylinder Lenses](#) for Circularizing Beams
- Negative Focal Length

TECHSPEC® Imaging Grade PCV Cylinder Lenses are typically used to diverge collimated light in a single axis. These lenses are designed for system integration due to the tightly controlled specifications and generous volume discounts. TECHSPEC Imaging Grade PCV Cylinder Lenses feature tightly controlled wedge and tilt specifications and are ideal for circularizing elliptical beams in combination with our [TECHSPEC Imaging Grade PCX Cylinder Lenses](#).

## Coating Curves

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

