

TECHSPEC® 25mm Dia. x 3mm 635-670/1064nm, Dual Band Laser Mirror



Stock #20-599 20+ In Stock

-

1

+

£144^{.80}

ADD TO CART

Volume Pricing	
Qty 1-5	£144.80 each
Qty 6-25	£127.20 each
Qty 26+	£123.08 each
Need More?	Request Quote

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

Clear Aperture (%):

>90

Commercial Polish	Back Surface:
25.00 +0.0/-0.2	Diameter (mm):
3.00 ±0.2	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
99.5	Reflection at DWL (%):
R _{abs} >99.5% @ 635, 670 & 1064nm	Coating Specification:
λ/10	Surface Flatness (P-V):
Dielectric	Coating Type:
Laser Mirror (635, 670, 1064nm)	Coating:
635, 670, 1064	Design Wavelength DWL (nm):
45	Angle of Incidence (°):
Fused Silica (Corning 7980)	Substrate: □
20 J/cm² @ 20ns	Damage Threshold, Reference: □
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- >99% Reflectivity at Design Wavelengths
- 10-5 Surface Quality for Sensitive Laser Applications
- 532/1064nm, 635-670/1064nm, or 800/1030nm Wavelength Bands
- TECHSPEC® Nd:YAG Laser Line Mirrors Also Available

TECHSPEC® Dual Band Laser Line Mirrors feature high reflectivity, excellent surface quality, and precision surface flatness to minimize scattering effects. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in a variety of standard sizes. TECHSPEC® Dual Band Laser Line Mirrors are ideal for beam steering applications in both laboratory and OEM laser systems. These mirrors are available in a 532/1064nm, 635-670/1064nm, and 800/1030nm dual band coating options for Nd:YAG lasers and red and green guide beams.