



TECHSPEC® 25mm Dia., NIR Broadband Dielectric, λ /10 Stemmed Mirror



Stock #16-736 3-4 DAYS

- 1 + **£134.30**

ADD TO CART

Qty 1-5

£134.30

Qty 6+

£107.52

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 λ /10

Substrate: Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R_{avg} ≥98% @ 750 - 1100nm (0 - 45°, All Polarizations) R_{avg} ≥99% @ 750 - 110nm (0 - 45°, S-Polarization)
Coating: Dielectric Mirror (750-1100nm)
Coating Type: Dielectric
Clear Aperture (%): 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 750 - 1100
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20
Damage Threshold, Reference: 1J/cm², 20ns, 20Hz @ 1064nm

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View