

TECHSPEC® 25mm Dia 0.25 NA, UV Coated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#33-954** 3-4 DAYS

[Other Coating Options](#)



1



£454.75

ADD TO CART

Qty 1-5

£454.75

Qty 6+

£363.80

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm): 50.00 @ 587.6nm
Numerical Aperture NA: 0.25
Back Focal Length BFL (mm): 46.50
Substrate:  Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 587.6
Asphere Figure Error, RMS @ 632.8nm: 1.2λ
Coating: UV (250-425nm)
Coating Specification: R _{avg} ≤1.5% @ 250 - 425nm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 1.61
Center Thickness CT (mm): 5.13 ±0.1
f/#: 2.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 250 - 425
Conjugate Distance: Infinite
Power (diopters): 20.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant