


**TECHSPEC® 25mm Dia., 1mm Thick, UV-AR Coated, λ/4 Fused Silica Window**

TECHSPEC® λ/4 UV Fused Silica Windows

Stock #72-359 **1 In Stock**   £125<sup>.60</sup>**ADD TO CART**

Volume Pricing	
Qty 1-5	£125.60 each
Qty 6-25	£100.00 each
Qty 26-49	£93.60 each
Need More?	<a href="#">Request Quote</a>

• Prices shown are exclusive of VAT/local taxes**Product Downloads****SPECIFICATIONS****General**

Type:

Protective Window

## Physical & Mechanical Properties

Bevel:	Protective as needed
Clear Aperture (%):	90
Clear Aperture CA (mm):	22.50
Diameter (mm):	25.00 +0.00/-0.10
Thickness (mm):	1.00 ±0.10
Edges:	Fine Ground
Knoop Hardness (kg/mm <sup>2</sup> ):	522.00
Parallelism (arcmin):	<1
Poisson's Ratio:	0.16
Young's Modulus (GPa):	73

## Optical Properties

Abbe Number (v <sub>d</sub> ):	67.8
Coating:	UV-AR (250-425nm)
Coating Specification:	$R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$ $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$
Index of Refraction (n <sub>d</sub> ):	1.458
Substrate:	Fused Silica (Coming 7980)
Surface Quality:	40-20
Transmitted Wavefront, P-V:	$\lambda/4$
Wavelength Range (nm):	250 - 450
Damage Threshold, Reference:	3 J/cm <sup>2</sup> @ 355nm, 10ns

## Material Properties

Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> °C):	0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Density (g/cm <sup>3</sup> ):	2.20

## Regulatory Compliance




RoHS 2015:	Compliant
Certificate of Conformance:	<a href="#">View</a>
REACH 2015:	Compliant

## PRODUCT DETAILS

- Available Uncoated or BBAR Coated for UV, Visible, and NIR
- Ideal for Imaging Applications
- Circular and Rectangular Sizes from 5 to 200mm
- [1A](#) or [λ/10](#) UV Fused Silica Windows Also Available


TECHSPEC®  $\lambda/4$  UV Fused Silica Windows are manufactured with 40-20 surface quality and  $\lambda/4$  transmitted wavefront error specifications, making them ideal for imaging applications. Featuring UV fused silica substrates, these windows provide high transmission from the ultraviolet (UV) through the visible and near-infrared (NIR). Broadband anti-reflection (BBAR) coating options are available to minimize reflection losses and increase transmission. TECHSPEC  $\lambda/4$  UV Fused Silica Windows are used in optical imaging applications, in low to medium powered laser applications, and as protective windows, especially in applications requiring transmission of UV light.

## TECHNICAL INFORMATION



## FUSED SILICA


### Uncoated Fused Silica Typical Transmission



Typical transmission of a 3mm thick, uncoated fused silica window across the UV - NIR spectra.

[Click Here to Download Data](#)

### Fused Silica with $\text{MgF}_2$ Coating Typical Transmission



Typical transmission of a 3mm thick fused silica window with  $\text{MgF}_2$  (400-700nm) coating at 0° AOI.


The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{\text{avg}} \leq 1.75\% @ 400 - 700\text{nm}$  (N-BK7)

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)

### Fused Silica with UV-AR Coating Typical Transmission




Typical transmission of a 3mm thick fused silica window with UV-AR (250-425nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.0\% @ 250 - 425\text{nm}$   
 $R_{avg} \leq 0.75\% @ 250 - 425\text{nm}$   
 $R_{avg} \leq 0.5\% @ 370 - 420\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with UV-VIS (250-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{abs} \leq 1.0\% @ 350 - 450\text{nm}$   
 $R_{avg} \leq 1.5\% @ 250 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with VIS-EXT (350-700nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:

$R_{avg} \leq 0.5\% @ 350 - 700\text{nm}$

Data outside this range is not guaranteed and is for reference only.

[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with VIS-NIR (400-1000nm) coating at 0° AOI.

The blue shaded region indicates the coating design wavelength range, with the following specification:


$R_{abs} \leq 0.25\% @ 880\text{nm}$   
 $R_{avg} \leq 1.25\% @ 400 - 870\text{nm}$   
 $R_{avg} \leq 1.25\% @ 890 - 1000\text{nm}$

Data outside this range is not guaranteed and is for reference only.


[Click Here to Download Data](#)




Typical transmission of a 3mm thick fused silica window with VIS




### Fused Silica with YAG-BBAR Coating Typical Transmission



### Fused Silica with NIR I Coating Typical Transmission



### Fused Silica with NIR II Coating Typical Transmission



## CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries

- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

---