

TECHSPEC[®] 25mm Dia. 355nm 45°, Nd:YAG Laser Line Mirror



TECHSPEC[®] Nd:YAG Laser Line Mirrors



Stock **#47-324** **20+ In Stock**

-

1

+

£139^{.20}

ADD TO CART

Volume Pricing	
Qty 1-5	£139.20 each
Qty 6-25	£122.40 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

Laser Mirror

Physical & Mechanical Properties

Parallelism (arcmin):

<3

>90	Clear Aperture (%)
Ground	Back Surface
25.00 +0.00/-0.20	Diameter (mm)
6.00 ±0.20	Thickness (mm)
Optical Properties	
10-5	Surface Quality
99.5	Reflection at DWL (%)
Coating Specification: R _{abs} >99.5% @ 355nm @45° AOI R _{avg} >99.5% @ 351 - 358nm @45° AOI	
351 - 358	Wavelength Range (nm)
λ/10	Surface Flatness (P-V)
Dielectric	Coating Type
Laser Mirror (355nm)	Coating
355	Design Wavelength DWL (nm)
45	Angle of Incidence (°)
Fused Silica (Corning 7980)	Substrate: □
6 J/cm² @ 355nm, 20ns, 20Hz	Damage Threshold, Reference: □

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Up to 99.9% Reflectivity at Nd:YAG Harmonic Frequencies
 - High Laser Induced Damage Threshold Specifications
 - 10-5 Surface Quality for Reduced Scatter in Sensitive Laser Applications
 - TECHSPEC® Laser Mirror Substrates and TECHSPEC® Yb:YAG Laser Line Mirrors Also Available
- TECHSPEC® Nd:YAG Laser Line Mirrors combine high reflectivity, excellent surface quality, and precision surface flatness to meet the requirements of demanding Nd:YAG laser applications. Each coating design has been tested to ensure a high laser damage threshold for compatibility with pulsed laser systems. These fused silica substrate laser mirrors have excellent thermal stability and are available in round, square, and rectangular profiles. TECHSPEC® Nd:YAG Laser Line Mirrors are ideal for laboratories and integration into larger laser systems. 266nm, 355nm, 532nm, 1064nm, and multi-line Nd:YAG mirror coatings are available.
- Note:** Contact us for customizable wavelengths, sizes, and varying AOI versions.

Compatible Mounts