See all 6 Products in Family

25mm Dia. x 200mm FL Uncoated, DCX N-K5 Lens

Stock **#32-902** CLEARANCE **20+ In Stock**

- 1 + **£16**.76

ADD TO CART

Volume Pricing	
Qty 1+	**£16.76** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Double-Convex Lens

Physical & Mechanical Properties

Diameter (mm):
25.00 +0.00/-0.10

Centering (arcmin):
<1

Center Thickness CT (mm):
5.00 ±0.10

Edge Thickness ET (mm):
4.25

Clear Aperture CA (mm):
24

Bevel:
Protective as needed

Optical Properties

Effective Focal Length EFL (mm):
200.00 @ 587.6nm

Back Focal Length BFL (mm):
198.35

Coating:
Uncoated

Substrate:
N-K5

Surface Quality:
40-20

Power (P-V) @ 632.8nm:
1.5λ

Irregularity (P-V) @ 632.8nm:
λ/4

Focal Length Tolerance (%):
±1

f/#:
8.00

Numerical Aperture NA:
0.06

Wavelength Range (nm):
330 - 2500

Regulatory Compliance

Certificate of Conformance:
View

Product Details

- N-K5 Substrate
- Various Anti-Reflection (AR) Coatings
- PCX and DCX Options Available

N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

Technical Information



Compatible Mounts

;