


TECHSPEC® 25mm Dia., 3mm Thick, UV-AR Coated λ/10 Fused Silica Window



Stock #65-875 In Stock

⊖ 1 ⊕ **£133.88**

ADD TO CART

Qty 1-5

£133.88

Qty 6+

£107.10

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
67.8

Bevel:
Protective as needed

Clear Aperture (%):
80

Clear Aperture CA (mm):
20.00

Diameter (mm):
25.00 +0.00/-0.20

Thickness (mm):
3.00 ±0.10

Coating:
UV-AR (250-425nm)

Coating Specification:
R_{abs} ≤1.0% @ 250 - 425nm
R_{avg} ≤0.75% @ 250 - 425nm
R_{avg} ≤0.5% @ 370 - 420nm

Coefficient of Thermal Expansion CTE (10⁻⁶/°C):
0.52 (+5 to +35°C)
0.57 (0 to +200°C)
0.48 (-100 to +200°C)

Density (g/cm³):
2.20

Edges:
Fine Ground

Index of Refraction n_d:
1.458

Knoop Hardness (kg/mm²):
522

Parallelism (arcsec):
<5

Poisson's Ratio:
0.16

Substrate:
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Transmitted Wavefront, P-V:
λ/10

Type:
Protective Window

Wavelength Range (nm):
250 - 450

Young's Modulus (GPa):
73

Damage Threshold, Reference: □
3 J/cm² @ 355nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)