

TECHSPEC® 25mm Dia. Linear Polarizer (XP42-100)



Stock #19-952 **20+ In Stock**

- 1 + £18⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-10	£18.60 each
Qty 11-25	£15.12 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Linear Polarizer **Type:**

Note:
Polarization axis can be identified as follows:
Circular Parts - Parallel to direction of notch on polarizer
Square Parts - Parallel to mark on protective film
Rectangular Parts - Parallel to first listed dimension

Physical & Mechanical Properties

25.00 +0.0/-0.3 **Diameter (mm):**

1.02 ±0.25 **Thickness (mm):**

Polarizing Film on PMMA **Construction:**

Optical Properties

up to 9000:1 (nominal at 555nm) **Extinction Ratio:**

[Polymer Film XP42-100](#) **Substrate:** □

Single: 42 ±2
Parallel: 36.4
Crossed: <0.004 (nominal at 555nm) **Transmission (%):**

400 - 700 **Wavelength Range (nm):**

>99.98 (nominal at 555nm) **Polarization Efficiency (%):**

<±5 **Transmission Variance after 1000 Hours (%):**

Environmental & Durability Factors

-10 to +60 **Operating Temperature (°C):**

≤80% (no condensation) **Operating Humidity:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 247:**

Product Details

- High Transmission of Unpolarized Light from 400 – 700nm
- Excellent Extinction Ratio of 9000:1
- Available in Custom Sizes
- [High-Temperature](#) Options Also Available



Ideal for a range of imaging applications, TECHSPEC® High Contrast Linear Polarizing Film (XP42) features an excellent extinction ratio and high transmission from 400 – 700nm. This polarizing film is offered in multiple thicknesses; thicker polarizing film has increased rigidity. Available in sheets, TECHSPEC® High Contrast Linear Polarizing Film (XP42) can be cut to fit any application need.

Note: Polarizer Film with adhesive available.

Immediate Custom Quotes Available

If you have a need for any round, square, or rectangular size of a TECHSPEC High Contrast Linear Polarizing Film (XP42) in dimensions between 3mm and 600mm, please visit our [Polarizing Film Tool](#). We'll provide an immediate quote, and can deliver the part to your requested size in approximately 3 weeks. A full list of standard manufacturing tolerances and restrictions are listed. For fully customized polymer polarizers to your requirements, visit our [Customized Polymer Polarizers Capabilities](#) page.

Technical Information



XP44 - Linear Polarizer

