

TECHSPEC® 25mm Dia. x 125mm FL, VIS-NIR Coated, UV Double-Convex Lens



UV Fused Silica Double-Convex (DCX) Lenses



Stock #63-842 3-4 DAYS

[Other Coating Options](#)



1



£122.83

ADD TO CART

Qty 1-5

£122.83

Qty 6+

£98.17

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Back Focal Length BFL (mm): 123.82
Effective Focal Length EFL (mm): 125.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.42 ±0.10
Edge Thickness ET (mm): 2.05
Radius R₁=R₂ (mm): 114.08
Clear Aperture CA (mm): 24.00
f#: 5.00
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.10
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000
Damage Threshold, Reference: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant