

TECHSPEC<sup>®</sup> 25mm Dia. x 60mm FL 633nm V-Coat, UV PCX Lens



Stock **#34-118** 2 In Stock

[Other Coating Options](#)

-

1

+

£140<sup>.00</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-5        | £140.00 each                  |
| Qty 6-25       | £112.00 each                  |
| Qty 26-49      | £104.80 each                  |
| Need More?     | <a href="#">Request Quote</a> |

!

 Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Plano-Convex Lens

Type:

Physical & Mechanical Properties

|                                         |                           |
|-----------------------------------------|---------------------------|
| 25.00 +0.0/-0.025                       | Diameter (mm):            |
| ≤1                                      | Centering (arcmin):       |
| 4.50 ±0.10                              | Center Thickness CT (mm): |
| 1.5                                     | Edge Thickness ET (mm):   |
| 24                                      | Clear Aperture CA (mm):   |
| Protective as needed                    | Bevel:                    |
| Fine Ground, Protective Bevel as Needed | Edges:                    |

Optical Properties

|                                             |                                  |
|---------------------------------------------|----------------------------------|
| 60.00 @ 587.6nm                             | Effective Focal Length EFL (mm): |
| 56.92                                       | Back Focal Length BFL (mm):      |
| Laser V-Coat (633nm)                        | Coating:                         |
| R <sub>abs</sub> <0.25% @ 633nm             | Coating Specification:           |
| <a href="#">Fused Silica</a> (Corning 7980) | Substrate: □                     |
| 40-20                                       | Surface Quality:                 |
| 1.5λ                                        | Power (P-V) @ 632.8nm:           |
| λ/4                                         | Irregularity (P-V) @ 632.8nm:    |
| ±1                                          | Focal Length Tolerance (%):      |
| 27.51                                       | Radius R <sub>1</sub> (mm):      |
| 2.4                                         | f/#:                             |
| 0.21                                        | Numerical Aperture NA:           |
| 633                                         | Design Wavelength DWL (nm):      |
| 5 J/cm <sup>2</sup> @ 633nm, 10ns           | Damage Threshold, By Design: □   |

Regulatory Compliance

|                           |                             |
|---------------------------|-----------------------------|
| <a href="#">Compliant</a> | RoHS 2015:                  |
| <a href="#">View</a>      | Certificate of Conformance: |
| <a href="#">Compliant</a> | Reach 235:                  |

## Product Details

- <0.25% Reflection at 633nm for HeNe Applications
- 5 - 50mm Diameters Available
- 10 - 250mm EFL Designs Available
- [405nm](#), [532nm](#), [1064nm](#), and [1550nm](#) V-Coated Options Offered

TECHSPEC® Laser Line Coated Fused Silica PCXLenses are available in a variety of laser line V-Coat AR coating options. Designed for maximum throughput at the specified laser wavelength, these lenses are ideal for applications utilizing low power HeNe, Diode, and Nd:YAG laser sources. With a maximum reflection of <0.25% per surface at the design wavelength, the lenses will provide superior transmission in applications utilizing multiple optical components.><0.25%>

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

# Compatible Mounts

---