

TECHSPEC[®] 25mm Dia. x 75mm FL 405nm V-Coat, UV PCX Lens



TECHSPEC 405nm Laser Line Coated Fused Silica PCXLenses



Stock **#34-073** 3-4 DAYS

[Other Coating Options](#)



1



£131.75

ADD TO CART

Qty 1-5

£131.75

Qty 6+

£105.40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm): 75.00 @ 587.6nm
Back Focal Length BFL (mm): 71.96
Coating: Laser V-Coat (405nm)
Coating Specification: R_{abs} <0.25% @ 405nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 4.43 ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁ (mm): 34.39
Clear Aperture CA (mm): 24
f/#: 3.00
Numerical Aperture NA: 0.17
Design Wavelength DWL (nm): 405
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 3 J/cm² @ 405nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant