

TECHSPEC® 25mm Dia. x 3mm Thick, BBAR (2000-5000nm) Coated Barium Fluoride Window



Stock #23-529 7 In Stock

-

1

+

£275<sup>.20</sup>

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1-10       | £275.20 each                  |
| Qty 11-25      | £247.20 each                  |
| Qty 26-49      | £233.60 each                  |
| Need More?     | <a href="#">Request Quote</a> |

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Protective Window

Type:

Physical & Mechanical Properties

Protective as needed

Bevel:

90.00

Clear Aperture (%):

|                 |                          |
|-----------------|--------------------------|
| 22.50           | Clear Aperture CA (mm):  |
| 25.00 +0.0/-0.1 | Diameter (mm):           |
| 3.00 ±0.1       | Thickness (mm):          |
| Fine Ground     | Edges:                   |
| 82.00           | Knoop Hardness (kg/mm²): |
| <3              | Parallelism (arcmin):    |
| 0.34            | Poisson's Ratio:         |
| 53              | Young's Modulus (GPa):   |

| Optical Properties                                                                                                    |                                        |
|-----------------------------------------------------------------------------------------------------------------------|----------------------------------------|
| 81.78                                                                                                                 | Abbe Number (v <sub>d</sub> ):         |
| Random                                                                                                                | Axis Orientation:                      |
| BBAR (2000-5000nm)                                                                                                    | Coating:                               |
| R <sub>avg</sub> <1.5% @ 2000-5000nm<br>R <sub>abs</sub> <3.0% @ 2000-5000nm<br>R <sub>avg</sub> <1.75% @ 2000-4000nm | Coating Specification:                 |
| 1.48                                                                                                                  | Index of Refraction (n <sub>d</sub> ): |
| Barium Fluoride (BaF <sub>2</sub> )                                                                                   | Substrate:                             |
| λ/2                                                                                                                   | Surface Flatness (P-V):                |
| 60-40                                                                                                                 | Surface Quality:                       |
| 2000 - 5000                                                                                                           | Wavelength Range (nm):                 |



| Material Properties |                                                              |
|---------------------|--------------------------------------------------------------|
| 18.1                | Coefficient of Thermal Expansion CTE (10 <sup>-6</sup> /°C): |
| 4.89                | Density (g/cm³):                                             |

| Regulatory Compliance |                             |
|-----------------------|-----------------------------|
| Compliant             | RoHS 2015:                  |
| View                  | Certificate of Conformance: |
| Compliant             | Reach 235:                  |

## Product Details

- Excellent Transmission from 200nm - 12μm
  - Resistant to High-Energy Radiation
  - Provide High Transmission without AR Coatings
- TECHSPEC® Barium Fluoride (BaF<sub>2</sub>) Windows can be used in a variety of applications, such as infrared spectroscopy, due to their wide broadband transmission that extends from the deep ultraviolet to the long-wave infrared. Barium fluoride's low index of refraction of 1.48 provides high transmission without the need for anti-reflection coatings. Barium fluoride windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range. While barium fluoride windows are less resistant to water than calcium fluoride, BaF<sub>2</sub> windows are the most resistant optical fluoride to high-energy radiation, but feature lower UV transmittance. BaF<sub>2</sub> has a Knoop hardness of 82.
- Note:** These optical windows are very sensitive to thermal shock.
- Barium fluoride is a fast scintillator and can be used to detect X-rays, gamma rays, or other high energy particles such as 511 keV gamma photons in Positron Emission Tomography (PET). BaF<sub>2</sub> can also be used to detect high-energy neutrons and separate them from simultaneously occurring gamma photons using pulse shape discrimination techniques.

## Technical Information



### Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

### Compatible Mounts