See all 10 Products in Family

25mm Diameter IR Cut-Off Filter



Stock **#53-710** CONTACT US

- 1 + **£41.60**

ADD TO CART

Volume Pricing	
Qty 1-24	**£41.60** each
Qty 25-49	**£37.60** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:

IR Cut-Off Filter

Physical & Mechanical Properties

Diameter (mm):

25.00 ±0.25

Thickness (mm):

1.10 ±0.25

Clear Aperture (%):
≥90

Edges:
Ground

Optical Properties

Cut-Off Wavelength (nm):
710.00

Substrate:
BOROFLOAT®

Coating:
Traditional Coated

Index of Refraction (n_d):
1.472

Surface Quality:
80-50

Coating Specification:
Surface 1: T=50% @ 710±30nm, T_{avg} >85% @ 480 - 680nm, T_{avg} <10% @ 740 - 1200nm
Surface 2: λ/4 MgF_2

Wavelength Range (nm):
480 - 1200

Environmental & Durability Factors

Operating Temperature (°C):
<250

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
View

Reach 247:
Compliant

Product Details

- 710nm Cut-Off Wavelength
- Circular and Rectangular Options
- Various Sizes Available

IR Cut-Off Filters are ideal for eliminating illumination beyond the visible spectrum in many visual and detector-based applications. These filters feature a 710nm cut-off wavelength. IR Cut-Off Filters are traditionally coated and have a BOROFLOAT® substrate. BOROFLOAT® is about three times more resistant to thermal shock than standard soda lime glass. IR Cut-Off Filters are available in circular and rectangular versions with various sizes for each.

Technical Information



Quote Your Size

Compatible Mounts

;