

TECHSPEC[®] 25mm Dia. x 500mm FL, VIS 0° Coated, Achromatic Lens



Stock **#47-651** 3-4 DAYS
[Other Coating Options](#)

-

1

+

£93.50

ADD TO CART

Qty 1-5
£93.50
Qty 6+
£74.80
Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

500.00
Focal Length Tolerance (%) : ±1
Back Focal Length BFL (mm) : 497.57
Focal Length Specification Wavelength (nm) : 587.6
Clear Aperture CA (mm) : 24.00
Centering (arcmin) : <1
Center Thickness CT (mm) : 5.50 ±0.20
Center Thickness CT 1 (mm) : 3.00 ±0.10
Center Thickness CT 2 (mm) : 2.50 ±0.10
Radius R₁ (mm) : 290.71
Radius R₂ (mm) : -232.07
Radius R₃ (mm) : -750.52
Edge Thickness ET (mm) : 5.13
Substrate: N-BK7 / N-SF5
Surface Quality : 40-20
f/# : 20.00
Numerical Aperture NA : 0.03
Coating : VIS 0° (425-675nm)
Coating Specification : R _{avg} ≤0.4% @ 425 - 675nm
Power (P-V) @ 632.8nm : 1.5λ
Irregularity (P-V) @ 632.8nm : λ/4
Bevel : Protective bevel as needed
Type : Achromatic Lens
Wavelength Range (nm) : 425 - 675

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View