

TECHSPEC® 25mm Dia. x 50mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-356** ☐ In Stock
[Other Coating Options](#)

1 **£100.30**

ADD TO CART

Qty 1-5
£100.30
Qty 6+
£80.33
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

50.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 43.53
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 24.00
Centering (arcmin): <1
Center Thickness CT (mm): 11.50 ±0.20
Center Thickness CT 1 (mm): 9.00 ±0.10
Center Thickness CT 2 (mm): 2.50 ±0.10
Radius R₁ (mm): 34.53
Radius R₂ (mm): -21.98
Radius R₃ (mm): -214.63
Edge Thickness ET (mm): 8.79
Substrate: ☐ N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 2.00
Numerical Aperture NA: 0.25
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View