

TECHSPEC®

25mm Dia. x 60mm FL 532nm V-Coat, UV PCX Lens



Stock #34-095 3-4 DAYS

[Other Coating Options](#)



1



£131.75

ADD TO CART

Qty 1-5

£131.75

Qty 6+

£105.40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.025

Effective Focal Length EFL (mm):

60.00 @ 587.6nm
Back Focal Length BFL (mm): 56.92
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): ≤1
Center Thickness CT (mm): 4.50 ±0.10
Edge Thickness ET (mm): 1.5
Radius R₁ (mm): 27.51
Clear Aperture CA (mm): 24
f/#: 2.4
Numerical Aperture NA: 0.21
Design Wavelength DWL (nm): 532
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Edges: Fine Ground, Protective Bevel as Needed
Damage Threshold, By Design: ☐ 5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant