See all 5 Products in Family

25mm Fixed Focal Length Lens

#86-210

Stock **#86-208** CONTACT US

- 1 + **£1,430**.00

ADD TO CART

Volume Pricing	
Qty 1+	**£1,430.00** each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Series:
4/3" Format Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Iris Option:

Variable

Length (mm):
89.00

Maximum Diameter (mm):
45.0

Outer Diameter (mm):
45

Weight (g):
250.00

Optical Properties

Horizontal Field of View @ Max Sensor Format:
40.9

Field of View @ Min Working Distance (mm):
125.00

Maximum Image Circle (mm):
21.60

Focal Length FL (mm):
25.00

Working Distance (mm):
150 - ∞

Aperture (f/#):
f/2 - f/16

Distortion (%):
<-0.6

Maximum Distortion (%):
-0.57

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
4/3"

Pixel Size (µm):
5.00

Threading & Mounting

Filter Thread:
M40.5 x 0.50

Mount:
C-Mount

Regulatory Compliance

RoHS 2015:
Exempt

Certificate of Conformance:
View

REACH 241:
Contains SVHC(s)

Product Details

- Up to 1", C-Mount Lens
- Less than 1.0% TV Distortion
- 12mm to 50mm Focal Length

Available in multiple focal lengths, 4/3" Format Fixed Focal Length Lenses incorporate a floating focus with aspheric lenses to maximize resolution across their entire working distance. Ideal for many machine vision applications, these fixed focal length lenses feature a broadband anti-reflection (AR) coating for maximum transmission. 4/3" Format Fixed Focal Length Lenses are available with focal lengths ranging from 12 - 50mm.

;