

TECHSPEC®

25mm Dia x 75mm FL 8-12µm Coated, Ge Aspheric Lens



Stock **#68-258**

3-4 DAYS

Other Coating Options



1



£807.50

ADD TO CART

Qty 1-5

£807.50

Qty 6+

£646.00

Volume Pricing

Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):

25.00 +0.0/-0.1

Effective Focal Length EFL (mm):

75.00 @ 4000nm

Numerical Aperture NA:

0.17

Back Focal Length BFL (mm): 72.30
Substrate: ☐ Germanium (Ge)
Aspheric Design Wavelength (nm): 4000
Asphere Figure Error, RMS @ 632.8nm: λ/6
Coating: BBAR (8000-12000nm)
Coating Specification: R _{avg} <3.0% @ 8 - 12μm
Centering (arcmin): ≤5
Surface Quality: 60-40
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 2.39
Center Thickness CT (mm): 2.80 ±0.10
f/#: 2.94
Bevel: Protective bevel as needed
Edges: Diamond Turned
Radius R₂ (mm): 78
Shape of Back Surface: Concave
Type: Aspheric Lens
Wavelength Range (nm): 8000 - 12000
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant