

## 25mm Focal Length Lens, 1" Sensor Format



25mm Focal Length Lens, 1" Sensor Format, #63-246

Stock **#63-246** **4 In Stock**

[Similar Products](#)

⊖ 1 ⊕ £609.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£609.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

1" Format Fixed Focal Length Lenses **Series:**  
Fixed Focal Length Lens **Type:**

### Physical & Mechanical Properties

Variable **Iris Option:**

43.00	<b>Length (mm):</b>
42.0	<b>Maximum Diameter (mm):</b>
42	<b>Outer Diameter (mm):</b>
125	<b>Weight (g):</b>

## Optical Properties

29.3°	<b>Horizontal Field of View, 1" Sensor:</b>
16.00	<b>Maximum Image Circle (mm):</b>
<-1.0	<b>TV Distortion (%):</b>
25.00	<b>Focal Length FL (mm):</b>
300 - ∞	<b>Working Distance (mm):</b>
f/1.4 - f/16	<b>Aperture (f/#):</b>
< -1.0%	<b>Maximum Distortion (%):</b>
VIS	<b>Lens Wavelength Range:</b>

## Sensor

1"	<b>Maximum Sensor Format:</b>
5.00	<b>Pixel Size (µm):</b>

## Threading & Mounting

M35.5 x 0.50	<b>Filter Thread:</b>
C-Mount	<b>Mount:</b>

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>

## Product Details

- Up to 1", C-Mount Lens
- "Fast" Lenses for Increased Throughput
- 4.7mm to 75mm Focal Length

1" Format Fixed Focal Length Lenses provide high throughput and high resolution across the entire camera sensor, allowing for excellent imaging even in less-than-ideal lighting conditions. Offered in 9 focal lengths from 4.7mm to 75mm, this complete family covers many of the applications in the market today. Engineered to minimize distortion, these lenses provide a perfect image for a human operator or an automated system. 1" Format Fixed Focal Length Lenses also feature a standard C-Mount lens mount for easy integration with the most common machine vision [cameras](#) we offer. All lenses feature front filter threading to attach to your choice of [optical filter](#).