

TECHSPEC® 25mm Diameter x 75mm FL, 532nm Coated, Laser Grade PCX Lens



TECHSPEC Laser Grade PCX Lenses

Stock **#67-965** 3-4 DAYS

[Other Coating Options](#)



1



£172.55

ADD TO CART

Qty 1-5

£172.55

Qty 6+

£137.70

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
75.00 @ 587.6nm

Back Focal Length BFL (mm):

71.96
Coating: Laser V-Coat (532nm)
Coating Specification: R _{abs} <0.25% @ 532nm
Substrate: ☐ Fused Silica (Corning 7980)
Surface Quality: 20-10
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/10
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 4.43 ±0.10
Edge Thickness ET (mm): 2.08
Radius R₁ (mm): 34.39
Clear Aperture CA (mm): 22.5
f/#: 3.00
Numerical Aperture NA: 0.17
Design Wavelength DWL (nm): 532
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Damage Threshold, By Design: ☐ 10 J/cm² @ 10ns

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View