

[See all 19 Products in Family](#)

3 x 3 x 15mm, 1064nm SHG, Type I LBO Nonlinear Crystal



Stock #11-173 **1 In Stock**

⊖ 1 ⊕ £356⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-2	£356.00 each
Qty 3+	£320.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Nonlinear Crystal

Type:

SHG @ 1064nm, Type I

Typical Applications:

LBO

Crystal Type:

<0.1mm x45°

Protective Chamfer:

Physical & Mechanical Properties

3.0x3.0 +0.0/-0.1 **Dimensions (mm):**

15.00 +0.0/-0.1 **Thickness (mm):**

<20 **Parallelism (arcsec):**

<5 **Perpendicularity (arcmin):**

Optical Properties

20-10 **Surface Quality:**

AR Coating **Coating:**

1064 **Design Wavelength DWL (nm):**

λ 10 **Surface Flatness (P-V):**

Coating Specification:
S1: 532 & 1064nm AR Coating
S2: 532 & 1064nm AR Coating

Damage Threshold, By Design:
10 J/cm² @ 1064nm, 10ns, 10Hz

Damage Threshold, Pulsed:
10 J/cm² @ 1064nm, 10ns, 10Hz

90/11.6 **Orientation Θ/Φ (°):**

Threading & Mounting

Unmounted **Mount:**

Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[Compliant](#) **Reach 219:**

[View](#) **Certificate of Conformance:**

Product Details

- BBO Crystals for Frequency Conversion of 800nm and 1030nm Lasers
- LBO Crystals for Frequency Conversion of 1030nm and 1064nm Lasers
- High Damage Thresholds Up to 10 J/cm² @ 1064nm, 10ns, 10Hz
- Broad Transparency Range from the UV to the IR

Nonlinear Crystals of either β -barium borate (BBO) or lithium triborate (LBO) are used for frequency conversion of laser sources. BBO crystals feature thicknesses from 0.2mm to 0.5mm to minimize group velocity mismatch and are ideal for frequency doubling or tripling of Ti:Sapphire and Yb:doped laser pulses. The critical and noncritical phase matching LBO crystals are ideal for second or third harmonic generation of Nd:YAG and Yb:doped lasers. Nonlinear Crystals with 20-10 surface quality and λ 10 (LBO) or λ 8 (BBO) surface flatness provide the broad transparency range and large nonlinear coefficient needed for the harmonic generation of fundamental laser frequencies. Each crystal features a protective anti-reflection (AR) coating that minimizes reflection and limits fogging from ambient conditions.