

[See all 37 Products in Family](#)

Richardson Gratings™ 300 Grooves, 25 x 25mm, 3µm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#15-773 20+ In Stock**

-

1

+

£156⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	£156.00 each
Qty 10-24	£140.40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General	
Reflective Diffraction Grating	Type:
1156	Master Reference:

Physical & Mechanical Properties	
25.0 x 25.0 ±0.1	Dimensions (mm):
>90	Clear Aperture (%):
Ruled Grating	Construction:
25.00	Length (mm):
6.00 ±0.5	Thickness (mm):
25.00	Width (mm):
±1	Centering of Ruled Area on Substrate (mm):
±0.15	Alignment of Grooves to Edge (°):
<0.05	Groove Spacing Tolerance (%):
Optical Properties	
300	Groove Density (grooves/mm):
1000 - 5000	Wavelength Range (nm):
3000 ±25	Blaze Wavelength (nm):
26.7	Blaze Angle (°):
72 (2nd order)	Peak Efficiency, Typical (%):
Aluminium	Coating:
Float Glass	Substrate: ☐
λ/4	Reflected Wavefront, RMS:
S and P	Polarization:
1	Spectral Order (m):
Regulatory Compliance	
View	Certificate of Conformance:

Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Excellent Efficiency at Blaze Wavelength and Blaze Angle
- Superior Dimensional Tolerances
- Ideally Suited for Spectroscopic Applications
- Custom Sizes Available

Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings are designed for consistent, predictable performance. The gratings are manufactured from highly accurate masters to provide a high level of repeatability to simplify OEM system designs by reducing the need for tedious alignment adjustments. With λ/4 reflected wavefronts and up to 90% diffraction efficiency, these gratings are specified to meet the needs of the most demanding applications such as high-resolution spectroscopy. Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings feature bare aluminum coatings, allowing for options that range from 250 to 10,000nm with excellent peak efficiencies. Custom sizes available on request.

Note: The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

Technical Information



Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools