

[See all 37 Products in Family](#)

# Richardson Gratings™ 300 Grooves, 12.5 x 12.5mm, 760nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock #37-118 [CONTACT US](#)

⊖ 1 ⊕ £124.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	£124.00 each
Qty 10-24	£111.60 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

## Product Downloads

## General

Reflective Diffraction Grating **Type:**

**Master Reference:**

## Physical & Mechanical Properties

12.5 x 12.5 ±0.1      **Dimensions (mm):**

>90      **Clear Aperture (%):**

Ruled Grating      **Construction:**

12.50      **Length (mm):**

6.00 ±0.5      **Thickness (mm):**

12.50      **Width (mm):**

±1      **Centering of Ruled Area on Substrate (mm):**

±0.15      **Alignment of Grooves to Edge (°):**

<0.05      **Groove Spacing Tolerance (%):**

## Optical Properties

300      **Groove Density (grooves/mm):**

450 - 1400      **Wavelength Range (nm):**

760 ±25      **Blaze Wavelength (nm):**

6.5      **Blaze Angle (°):**

79      **Peak Efficiency, Typical (%):**

Aluminium      **Coating:**

Float Glass      **Substrate:**

λ/4      **Reflected Wavefront, RMS:**

S and P      **Polarization:**

1      **Spectral Order (m):**

## Regulatory Compliance

[View](#)      **Certificate of Conformance:**

## Product Details


- Excellent Efficiency at Blaze Wavelength and Blaze Angle
- Superior Dimensional Tolerances
- Ideally Suited for Spectroscopic Applications
- Custom Sizes Available

Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings are designed for consistent, predictable performance. The gratings are manufactured from highly accurate masters to provide a high level of repeatability to simplify OEM system designs by reducing the need for tedious alignment adjustments. With λ/4 reflected wavefronts and up to 90% diffraction efficiency, these gratings are specified to meet the needs of the most demanding applications such as high-resolution spectroscopy. Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings feature bare aluminum coatings, allowing for options that range from 250 to 10,000nm with excellent peak efficiencies. Custom sizes available on request.


**Note:** The surface of these gratings is very sensitive and should never be touched when handling the optic. If cleaning is required to remove dust particles, non-contact cleaning using clean compressed air is recommended.

## Technical Information


**Typical Efficiency Curves for High Precision Reflection Gratings  
Optimized (Blaze) Wavelengths from 1200 - 1850nm**



Typical Efficiency Curves for High Precision Reflection Gratings  
Optimized (Blaze) Wavelengths from 750 - 900nm



Typical Efficiency Curves for High Precision Reflection Gratings  
Optimized (Blaze) Wavelengths from 300 - 400nm



## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



Component Handling Tools

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).