

300mm Cobra Max RGB-IR Line Light



300mm Cobra MaxLine Light



Stock **#73-952** NEW **1 In Stock**

-

1

+

£6,508^{.45}

ADD TO CART

Volume Pricing	
Qty 1+	£6,508.45 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

LED

Type of Illumination:

Note: Lights are fan cooled. See datasheet for additional mounting, spectral, and irradiance information	
ProPhotonix	Manufacturer:
Line Light	Geometry:
Illumination Mode: Ethernet Controlled, Continuous, Strobed	
Physical & Mechanical Properties	
300.00	Length (mm):
300.00 x 173.50	Dimensions (mm):
Collimated (M2)	Lens Position:
Optical Properties	
RGB-IR	Color:
455, 532.5, 630, 855	Wavelength:
10-112	Working Distance (mm):
Electrical	
120000	Maximum Trigger Frequency (Hz):
Hardware & Interface Connectivity	
Straight	Connector:
24	Operating Voltage (V):
Power Supply: Power supply required and sold separately: USA #73-977	
2m braided power cable included	Length of Cable (m):
Threading & Mounting	
Aluminum T-Slot Extrusion	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

PRODUCT DETAILS

- Intensities up to 3140kLux
 - 100, 300, or 600mm Length Options Available
 - White, Red, Multispectral, and SWIR Illumination Options Available
- ProPhotonix COBRA™ MAXLED Line Lights are slim, compact LED line lights available in lengths of 100, 300, or 600mm in red, white, multispectral, or SWIR illumination options. These line lights feature Chip-on-Board LED technology which offers greater uniformity, thermal performance, and intensity while maintaining a compact size compared to traditional surface mount LED constructions. ProPhotonix COBRA™ MAXLED Line Lights multispectral option offers RGB-IR illumination and the ability to control each wavelength independently. The available easy-to-use comprehensive software package can be customized to meet specific application needs and is downloadable from a QR code included with the units. These lights are ideal for many linescan inspection applications such as solar cell inspection, semiconductor inspection, food sorting, and flat panel display inspection.
- Note:** Required 24V Power Supply, [#73-977](#), sold separately. Optional Lens Kits are available to adjust the working distance by changing the position of the projection lens.