

300µm Aperture Diameter, Mounted, Precision Pinhole



300µm Aperture Diameter, Mounted, Precision Pinhole, #56-285

Stock #56-285 3-4 DAYS

⊖ 1 ⊕ **£63.75**

ADD TO CART

Qty 1-5

£63.75

Qty 6+

£56.27

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Mounted

Outer Diameter (mm):
25 +0.4/-0.000

Construction:
Stainless Steel

Fixed Aperture Diameter (μm):
300

Thickness (mm):
0.03 Nominal

Aperture Tolerance (μm):
 ± 5

Mount Thickness (mm):
 1.25 ± 0.05

Aperture Centration (μm):
 ± 125

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
