

## 2m Low Noise BNC to BNC Cable



Stock #90-649 **NEW** 1 In Stock

- 1 + £160.<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	£160.00 each
Need More?	<a href="#">Request Quote</a>

**!** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### Hardware & Interface Connectivity

Connector:  
BNC / BNC

Length of Cable (m):  
2

### Regulatory Compliance

RoHS 2015:  
**Compliant**

Certificate of Conformance:

## Product Details

- Ultra-Wide Adjustable Transimpedance Gain from  $10^2$  to  $10^{11}$  V/W
- Exceptional Low-Noise, High-Sensitivity Single-Beam Detection
- Optimized for Absolute Optical Power Measurements
- Designed for Direct, Alignment-Free Integration

Variable Gain Photoreceivers feature an ultra-wide adjustable transimpedance gain from  $10^2$  to  $10^{11}$  V/W, enabling precise measurement of optical signals across a broad power range. Engineered for ultra-low noise performance, these photoreceivers achieve noise equivalent power (NEP) as low as  $6\text{fW}/\sqrt{\text{Hz}}$ , ensuring accurate detection of extremely weak optical signals. Designed for single-beam detection, they provide maximum sensitivity and dynamic range, allowing for simple, alignment-free integration into optical systems. Variable Gain Photoreceivers are ideal for applications such as photonics research, optical communication testing, and precision low-light measurements.

**Note:** Power supply sold separately. Please see specifications for more details.

---