

TECHSPEC® 2mm Dia. x 4mm FL, VIS 0° Coated, Achromatic Lens



Stock #84-125 **CLEARANCE** 20+ In Stock

[Other Coating Options](#)

1 £190.⁴⁰

ADD TO CART

Volume Pricing

Qty 1+	£190.40 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Achromatic Lens **Type:**

Physical & Mechanical Properties

2.00 +0.0/-0.025 **Diameter (mm):**

Clear Aperture CA (mm):

1.6	
30-45	Centering (arcmin):
2.00 ±0.10	Center Thickness CT (mm):
1.00 ±0.05	Center Thickness CT 1 (mm):
1.00 ±0.05	Center Thickness CT 2 (mm):
1.72	Edge Thickness ET (mm):
Protective as needed	Bevel:
Optical Properties	
4.00	Effective Focal Length EFL (mm):
±1	Focal Length Tolerance (%):
2.92	Back Focal Length BFL (mm):
587.6	Focal Length Specification Wavelength (nm):
2.26	Radius R ₁ (mm):
-2.26	Radius R ₂ (mm):
-10	Radius R ₃ (mm):
N-PSK53A / N-LASP9	Substrate: <input type="checkbox"/>
20-10	Surface Quality:
2.00	f#:
0.25	Numerical Aperture NA:
VIS 0° (425-675nm)	Coating:
R _{avg} ≤0.4% @425 - 675nm	Coating Specification:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
425 - 675	Wavelength Range (nm):

Regulatory Compliance	
Compliant	Reach 181:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume


Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

Product Details

- Designed for 0° Angle of Incidence
- Less Than 0.4% Reflectance Per Surface from 425 - 675nm
- [MgF₂](#) and [VIS-NIR](#) Coated Achromats Also Available

TECHSPEC® VIS 0° Coated Achromatic Lenses consist of two optical components cemented together to form an achromatic doublet. The doublet is computer optimized to correct for on-axis spherical and chromatic aberrations.

Technical Information



Coating Curves