

[See all 13 Products in Family](#)

2X Objective, CFI Plan Achromatic UW

See More by [Nikon](#)



Stock #75-351 NEW **1 In Stock**

⊖ 1 ⊕ £412.⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1+ | £412.00 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

MRL00022 **Model Number:**

Compatible Tube Lens Focal Length (mm):
Focal Length: 200mm

Microscope Objective **Type:**

Infinity Corrected **Style:**

Nikon

Manufacturer:

Physical & Mechanical Properties

12 Field of View (mm):

52.40 Length excluding Threads (mm):

30 Maximum Diameter (mm):

120 Weight (g):

Optical Properties

N/A Compatible Cover Glass Thickness (mm):

3.2 Horizontal Field of View, 1/2" Sensor:

4.4 Horizontal Field of View, 2/3" Sensor:

2X Magnification:

0.06 Numerical Aperture NA:

7.5 Working Distance (mm):

25 Field Number (mm):

59.9 Parfocal Length (mm):

N/A Immersion Liquid:

Sensor

2/3" Maximum Sensor Format:

Threading & Mounting

M25 x 0.75 Mounting Threads:

Regulatory Compliance

[View](#) Certificate of Conformance:

Product Details

- Exceptional Flat-Field Imaging
- High Numerical Apertures and Oil Immersion Options Available
- Wide Magnification Range (1X to 100X)

Nikon's CFI Plan Achromat Objectives deliver exceptional flat-field imaging ensuring sharp, distortion-free clarity across the entire field of view, making these objectives ideal for both visual inspection and high-precision digital imaging. With high numerical apertures and specialized oil immersion options available, these objectives offer enhanced resolution and light-gathering capability for demanding high-magnification applications. Nikon CFI Plan Achromat Objectives are available in 1X up to 100X magnification, providing solutions for low-magnification overviews or detailed high-resolution imaging. Color corrected for the entire visible spectrum; these objectives are suitable for brightfield and fluorescence observation in routine lab work and photomicrography.

Technical Information

