


3.0 OD, 12.5mm Dia., NIR II Coated, Absorptive ND Filter

See More by [Hoya](#)



Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters

Stock **#13-232** 20+ In Stock

-

1

+

£48¹⁵

ADD TO CART

Volume Pricing	
Qty 1-10	£48.15 each
Qty 11-25	£42.02 each
Qty 26-49	£40.27 each
Need More?	Request Quote

Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Type:
Neutral Density Filter







Stock No. of Uncoated Filter:	
#48-533	
Physical & Mechanical Properties	
Diameter (mm):	
12.50	
Thickness (mm):	
3.00 ±0.5	
Dimensional Tolerance (mm):	
±0.1	
Parallelism (mm):	
<0.02	
Optical Properties	
Optical Density OD (Average):	
3 ±0.3 @ 400-700nm (Uncoated Filter)	
Nominal Optical Density @ Center of Coating:	
1.52 @ 1200nm	
Glass/Filter Number:	
Hoya ND0.3	
Substrate: □	
ND Filter Glass	
Coating:	
NIR II (750-1550nm)	
Index of Refraction (n _d):	
1.51	
Surface Quality:	
80-50	
Transmission (%):	
0.1 (average) @ 400 - 700nm	
Blocking Wavelength Range (nm):	
400 - 700	
Coating Specification:	
R _{abs} ≤1.5% @ 750 - 800nm	
R _{abs} ≤1.0% @ 800 - 1550nm	
R _{avg} ≤0.7% @ 750 - 1550nm	
Wavelength Range (nm):	
750 - 1550	
Material Properties	
Transformation Temperature (°C):	
490	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 250:	
Compliant	




PRODUCT DETAILS

- Optical Densities from 0.1 to 4.0
- VIS 0°, NIR I, and NIR II Coating Options
- 12.5, 25, and 50mm Diameter Sizes
- Uncoated [HOYA](#) or [SCHOTT](#) ND Filters Also Available

Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters feature HOYA colored glass substrates that are AR coated on both surfaces to reduce back reflections in the visible or near-infrared (NIR) spectra. VIS 0°, NIR I, and NIR II broadband AR coatings cover the spectral ranges of 425-675nm, 600-1050nm, and 750-1550nm. These neutral density filters attenuate light via absorption and can be stacked together to achieve custom optical densities to meet application requirements. Anti-Reflection (AR) Coated HOYA Absorptive Neutral Density (ND) Filters are ideal for use in imaging and detection applications to reduce stray light, as well as in general filter stacking applications to control intensity. The standard metric diameters of 12.5, 25, and 50mm are compatible with our [TECHSPEC® C, S, and T-Mount Circular Optic Mounts](#) for benchtop applications.

TECHNICAL INFORMATION





CUSTOM

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

COMPATIBLE MOUNTS