

**TECHSPEC®**

**30mm H x 30mm L x 50mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens**



Stock #25-502 **4 In Stock**

⊖ 1 ⊕ £139.<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	£139.00 each
Qty 6-25	£124.00 each
Qty 26-49	£119.00 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Cylinder Lens, Plano-Convex **Type:**

**Physical & Mechanical Properties**

6.00 ±0.1 **Center Thickness CT (mm):**

**Dimensional Tolerance (mm):**

+0.0/-0.2

Dimensions (mm):

30.0 x 30.0

Edge Thickness ET (mm):

1.20

Tilt Tolerance (mm):

±0.1 over H

Wedge Tolerance (arcmin):

15.00

## Optical Properties

Effective Focal Length EFL (mm):

50.00

Substrate:

N-BK7

f/#:

1.66

Numerical Aperture NA:

0.30

Coating:

MS 0° (425-675nm)

Wavelength Range (nm):

350 - 2200

Back Focal Length BFL (mm):

46.04

Coating Specification:

R<sub>avg</sub> ≤ 0.4% @ 425 - 675nm

Focal Length Tolerance (%):

±3

Radius R<sub>1</sub> (mm):

25.84

Surface Quality:

60-40

## Regulatory Compliance

Certificate of Conformance:

[View](#)

## Need different specs or modifications?

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).

## Product Details

- N-BK7 Substrate for Broadband Performance
- Cost-Effective for OEM Integration
- Multiple Coating Options Available

TECHSPEC® Illumination Grade PCX Cylinder Lenses are similar to Plano-Convex (PCX) lenses in profile, but include a portion of a cylinder instead of a sphere. These lenses focus light in one dimension and can transform a point of light into a line. TECHSPEC® Illumination Grade PCX Cylinder Lenses are available in circular and rectangular versions, along with multiple coating options. Cylinder lenses are ideal for line projection in machine vision applications or guidance systems.

**Note:** For negative focal length cylinder lenses, see our [TECHSPEC® Illumination Grade PCV Cylinder Lenses](#).

**LASER OPTICS** MADE BY EDMUND OPTICS®

[LEARN MORE](#)

## Technical Information



**PCX Rectangular**

Circular And Rectangular Cylinder Lenses



**PCX Circular**

## Coating Curves