

TECHSPEC® 30mm Dia. Protected Silver, λ/4 Mirror



Stock #88-537 [CONTACT US](#)

⊖ 1 ⊕ **£74.38**

ADD TO CART

Qty 1-5

£74.38

Qty 6+

£59.50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00

Surface Flatness (P-V):
λ/4

Substrate:
[BOROFLOAT®](#)

Back Surface:
Commercial Polish

Surface Quality:
60-40

Dimensional Tolerance (mm):
+0.0/-0.25

Coating Specification:
R_{avg} >98% @ 450 - 2000nm
R_{avg} >98% @ 2000 - 10,000nm

Coating:
Protected Silver (450-10000nm)

Coating Type:
Metal

Bevel:
Protective bevel as needed

Clear Aperture (%):
85

Edges:
Fine Ground

Thickness (mm):
3.00 ±0.25

Type:
Flat Mirror

Wavelength Range (µm):
0.45 - 10

Wavelength Range (nm):
450 - 10000

Damage Threshold, Reference:
0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
