

30mm Dia. x 17.5mm FL, Uncoated Molded Aspheric Condenser Lens



Molded Aspheric Condenser Lenses

Stock **#88-291** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£38.25

ADD TO CART

Qty 1-10

£38.25

Qty 11+

£33.66

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
30.00 +/-0.3

Effective Focal Length EFL (mm):
17.50 @ 587.6nm

Numerical Aperture NA:
0.86

Back Focal Length BFL (mm): 10.40
Substrate:  Liba2000+
Focal Length Tolerance (%): ±7
Coating: Uncoated
Centering (arcmin): ≤25
Surface Quality: 5/5 x0.63; E 0.4
Clear Aperture CA (mm): 24.00
Edge Thickness ET (mm): 2.6
Center Thickness CT (mm): 14.00 ±0.20
f/#: 0.58
Bevel: Protective bevel as needed
Diameter of Asphere (mm): 28.0
Radius R₂ (mm): 24.0
Shape of Back Surface: Convex
Type: Condenser Lens
Wavelength Range (nm): 350 - 2000
Conjugate Distance: Infinite
Note: Click here for more information on the ISO 10110 surface quality specification.

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant