

TECHSPEC® 30mm Dia. x 75mm FL, VIS-NIR Coated, Achromatic Lens



Stock **#49-373** 3-4 DAYS
[Other Coating Options](#)

- 1 + **£122.40**

ADD TO CART

Qty 1-5
£122.40
Qty 6+
£97.96
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
30.00 +0.0/-0.025

Effective Focal Length EFL (mm):

75.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 67.44
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 29.00
Centering (arcmin): <1
Center Thickness CT (mm): 11.40 ±0.20
Center Thickness CT 1 (mm): 8.40 ±0.10
Center Thickness CT 2 (mm): 3.00 ±0.10
Radius R ₁ (mm): 40.51
Radius R ₂ (mm): -38.68
Radius R ₃ (mm): -922.04
Edge Thickness ET (mm): 8.40
Substrate:  N-SBK8 / N-SF10
Surface Quality: 40-20
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant