

[See all 7 Products in Family](#)

35mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-684



Stock **#68-686** **3 In Stock**

[Similar Products](#)

⊖ 1 ⊕ £1,253⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£1,253.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Product Family:
Ultra High Resolution Fixed Focal Length Lenses

Type:
Fixed Focal Length Lens

Physical & Mechanical Properties

Variable	Iris Option:
49.00	Length (mm):
43.0	Maximum Diameter (mm):
43	Outer Diameter (mm):
160.00	Weight (g):

Optical Properties

17.0	Field of View @ Min Working Distance (mm):
17.0mm - 10.4°	Horizontal Field of View, 1/2" Sensor:
11.00	Maximum Image Circle (mm):
35.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/2 - f/16	Aperture (f/#):
<-0.05%	Maximum Distortion (%):
VS	Lens Wavelength Range:

Sensor

2/3"	Maximum Sensor Format:
2.40	Pixel Size (µm):

Threading & Mounting

M34 x 0.50	Filter Thread:
C-Mount	Mount:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- 2/3", C-Mount Lens
- Up to 10 MegaPixels, 2.4µm Pixel Size Sensors
- Spectral Range of 400 - 1000nm
- 5mm to 50mm Focal Lengths

Ultra High Resolution Fixed Focal Length Lenses are designed to provide 10 MegaPixel resolution on axis. These lenses have a spectral range of 400 to 1000nm. Through the use of a floating focus and aspheric lens elements, these high-resolution lenses are able to maintain excellent performance from 100mm to infinity. Ultra High Resolution Fixed Focal Length Lenses feature locking focus, iris rings, and a front filter thread to allow the use of standard optical filters for increased versatility. The lenses are available in 7 focal length options and feature very low distortion.