

30W Deuterium / 5W Tungsten Lamp



30W Deuterium / 5W Tungsten Lamp, #87-300

Stock **#87-300** [CONTACT US](#)

⊖ 1 ⊕ £3,160⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	£3,160.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:
Built-in power supply. AC power cord included. Fiber patchcord listed under Accessories tab sold separately.

Lamp Lifetime (hours):
≥2000 / ≥10,000

Physical & Mechanical Properties

Dimensions (mm):
220 x 187 x 130

Optical Properties

190 - 2500
Wavelength Range (nm):

Electrical

30W Deuterium
5W Tungsten
Output Power (W):

Hardware & Interface Connectivity

SMA-905
Connector:

Regulatory Compliance

[View](#)
Certificate of Conformance:

Product Details

- Designed for Use with [Spectrometers](#)
- Lamps Available for UV to NIR
- Xenon, Tungsten, or Deuterium Sources

Broadband Fiber-Coupled Light Sources are ideal for use in a variety of spectroscopy applications and for coupling with the Fiber Optic Reflectance Sphere. The pulsed Xenon source is designed for applications from the UV to visible. The Tungsten source is designed for applications in the visible to NIR. The Deuterium/Tungsten source is ideal for applications requiring wide spectral ranges from the UV to NIR.