

[See all 5 Products in Family](#)

# 38.1mm Dia., 4mm Thick, Uncoated, ISP Optics Barium Fluoride (BaF<sub>2</sub>) Window | BF-W-38-4

See More by [ISP Optics](#)



Stock #24-500 **CLEARANCE** 3 In Stock

1 £155<sup>16</sup>

**ADD TO CART**

Volume Pricing	
Qty 1+	£155.16 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

BF-W-38-4	<b>Model Number:</b>
Protective Window	<b>Type:</b>
	<b>Type of Window:</b>

Crystal

## Physical & Mechanical Properties

32.38 Clear Aperture CA (mm):

38.10 +0.00/-0.13 Diameter (mm):

4.00 ±0.13 Thickness (mm):

<3 Parallelism (arcmin):

Protective as needed Bevel:

85 Clear Aperture (%):

Fine Ground Edges:

0.34 Poisson's Ratio:

53 Young's Modulus (GPa):

82.00 Knoop Hardness (kg/mm<sup>2</sup>):

## Optical Properties

Uncoated Coating:

[Barium Fluoride \(BaF<sub>2</sub>\)](#) Substrate:

1.48 Index of Refraction (n<sub>d</sub>):

40-20 Surface Quality:

81.78 Abbe Number (v<sub>d</sub>):

Random Axis Orientation:

200 - 12000 Wavelength Range (nm):

2λ Surface Flatness (P-V):

## Material Properties

4.89 Density (g/cm<sup>3</sup>):

18.1 Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):

## Environmental & Durability Factors

Maximum: 800 Operating Temperature (°C):

## Regulatory Compliance

[Compliant](#) RoHS 2015:

[View](#) Certificate of Conformance:

[Compliant](#) Reach 240:

## Product Details

- Excellent Transmission from 0.2 - 12μm
- Resistant to High-Energy Radiation
- High Transmission without AR Coatings

ISP Optics Barium Fluoride (BaF<sub>2</sub>) Windows provide excellent transmission from 0.2- 12μm without the need for an Anti-Reflection (AR) coating due to its low index of refraction. Barium Fluoride has similar physical properties to Calcium Fluoride, but features higher resistance to high-energy radiation. This makes Barium Fluoride ideal for vacuum UV (VUV) applications such as thermography or laser spectroscopy where high radiation resistance is required. ISP Optics Barium Fluoride (BaF<sub>2</sub>) Windows can be used up to 800°C in a dry environment, but prolonged exposure to moisture can degrade transmission in the ultraviolet range.

**Note:** These optical windows are very sensitive to thermal shock.

## Special Handling

These optics require special handling to avoid damage and ensure long-term performance. Proper handling, cleaning, and storage are essential to maintain optical quality. Explore our [Optics Cleaning Resources](#) for step-by-step guides and best practices. For personalized assistance, [Email us](#) or [Chat](#) with our technical support team.



**Component Handling Tools**

---

;