

[See all 1 Products in Family](#)

32mm Dia. x -200mm FL, Grade 2, Double-Concave Lens



Stock #53-113 CLEARANCE 20+ In Stock

⊖ 1 ⊕ £9.⁰⁰

[ADD TO CART](#)

Volume Pricing

Qty 1+	£9.00 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Type:
Double-Concave Lens

Physical & Mechanical Properties

Diameter (mm):
32.00

Optical Properties

Effective Focal Length EFL (mm):
-200.00

6.25

f#:

0.08

Numerical Aperture NA:

Material Properties

Grade 2

Grade:

Regulatory Compliance

[View](#)

Certificate of Conformance:

Product Details

- Ideal for Experimenting and Prototyping Applications
- Quantities Extremely Limited, Buy While Supplies Last
- For Even More Deals, Check out [Mega Clearance: Optics](#)

Double-concave (DCV) lenses have two inward curved surfaces and a negative focal length. They are used for image reduction and to spread light.

Experimental Quality Double-Concave (DCV) Lenses are offered in several experimental grade options. Grade 1 is standard optical glass, edged, free of visible scratches, chips, stains, or oxidation. Grade 2 is unedged, non-optical glass, small chips, slight stains, or other defects. They may have slight edge cement separation.

Note: Specifications for experimental grade optics may vary as much as 10% from those listed. Also, no additional information is available other than what is provided.

Technical Information

