


3600 Grooves/mm, 40mm Dia., 220nm Rowland Circle Concave Diffraction Grating

See More by [ZEISS](#)



ZEISS Concave Diffraction Gratings



Stock #11-535 3-4 DAYS



1



£544.00

ADD TO CART

Qty 1+

£544.00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
3600 ±1

Blaze Wavelength (nm):
220

Diameter (mm):

40.00
Coating: Bare Aluminum
Substrate: 
Type: Rowland Circle
Diffraction Efficiency (%) : ≥50 @ 200nm ≥34 @ 300nm ≥32 @ 400nm
Radius of Curvature (mm): 298.50
Groove Profile: Sinusoidal
Angle of Incidence, α (°): -40
Diffraction Angle, β @ 200nm (°): -4.4
Diffraction Angle, β @ 300nm (°): -25.9
Object Distance, l_a @ 200nm: 228.7
Focal Distance, l_b @ 200nm: 297.6
Edge Thickness ET (mm): 8.0
Diffraction Area Diameter (mm): ≥33

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View