

38.4mm Diameter x 30mm FL, PCX Condenser Lens



Stock #43-594 **17 In Stock**

[Other Coating Options](#)

⊖ 1 ⊕ £41⁰⁰

ADD TO CART

| Volume Pricing | |
|----------------|-------------------------------|
| Qty 1-10 | £41.60 each |
| Qty 11-49 | £36.80 each |
| Need More? | Request Quote |

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Condenser Lens **Type:**

Physical & Mechanical Properties

38.40 +0.2/-0.4 **Diameter (mm):**

≤25 **Centering (arcmin):**

| | |
|---------------------------|---|
| 19.00 ±0.25 | Center Thickness CT (mm): |
| Protective as needed | Bevel: |
| Convex | Shape of Back Surface: |
| Optical Properties | |
| 30.00 | Effective Focal Length EFL (mm): |
| 0.64 | Numerical Aperture NA: |
| B270 | Substrate: <input type="checkbox"/> |
| ±7 | Focal Length Tolerance (%): |
| Uncoated | Coating: |
| 80-50 (typical) | Surface Quality: |
| 0.78 | f/#: |
| 58.5 | Abbe Number (v_d): |
| 1.523 | Index of Refraction (n_d): |
| 84.125 | Radius R₂ (mm): |
| 350 - 2500 | Wavelength Range (nm): |
| Infinite | Conjugate Distance: |

| | |
|----------------------------|---|
| Material Properties | |
| 9.4 | Coefficient of Thermal Expansion CTE (10⁻⁶/°C): |

| | |
|------------------------------|------------------------------------|
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |

Product Details

- Molded Illumination Lenses
- Aspheric or Spherical Designs
- High Numerical Apertures

Condenser Lenses are molded lenses designed for illumination applications. Featuring large apertures and short focal lengths, Condenser Lenses are commonly used in emitter-detector applications, projection applications, or condensing illumination applications such as Koehler Illumination. The Aspheric Condenser Lenses are molded on the aspheric surface and ground and polished on the opposite face, offering superior performance. The Plano-Convex (PCX) Condenser Lenses are molded on both surfaces, offering excellent value.

Technical Information



