

[See all 13 Products in Family](#)

365nm, Ethernet High Intensity Coaxial Spot Light (Recertified 05-P)

See More by [Advanced Illumination](#)



Advanced Illumination Ethernet Controlled High Intensity LED Spot Lights

Stock **#21-356-RCD-05P** RECERTIFIED **1 In Stock**

-
1
+
£424.⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	£424.00 each
Need More?	Request Quote

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

SL162-365C1 **Model Number:**

50,000 **LED Lifetime (hours):**

1 **Number of LEDs:**

LED Illuminator **Type of Illumination:**

Note:
Required Controller [#18-645](#); Required Power Supply [#66-855](#)

Advanced Illumination **Manufacturer:**

Spot Light **Geometry:**

Constant, Pulsed, Gated **Illumination Mode:**

Physical & Mechanical Properties

85.1 **Weight (g):**

Optical Properties

UV **Color:**

365 **Wavelength (nm):**

Hardware & Interface Connectivity

C1 **Connector:**

Power Supply:
Power Supply Required and Sold Separately:
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#89-513](#)
Korea: [#33-773](#)
China: [#66-855](#)

2 **Length of Cable (m):**

Environmental & Durability Factors

0 to +60 **Operating Temperature (°C):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

Product Details

- Controllable via Ethernet GUI or Web Browser
- Compatible with 8mm or 1/4" (0.312") Fiber Illumination Ports
- Efficient Thermal Management for Long LED Life
- Compatible with [TECHSPEC® Telecentric Backlight Illuminators](#) and [Lenses](#)

Advanced Illumination Ethernet Controlled High Intensity In-Line Lights utilize a C1 connector to connect to the DCS-100E Single Output Controller (#18-645). The DCS-100E Single Output Controller allows these high intensity in-line lights to be ethernet controlled through a downloadable software package or through a Web Based Graphical User Interface (GUI). With efficient thermal management, these in-line lights are able to provide 33,000 Lux at a working distance of 100mm with a spot size of 61mm in either a continuous, pulsed, or gated operating mode. Advanced Illumination Ethernet Controlled High Intensity In-Line Lights can be overdriven in short pulses without damaging the LED through Advanced Illumination's SignaTech™ Control System which is available with the DCS-100E Controller. These lights are available in UV, Blue, Green, Red Orange, IR, or White and are compatible with the 8mm port found on many in-line illumination imaging lenses, making them an excellent choice for use with TECHSPEC® Telecentric Backlight Illuminators and telecentric lenses with an [inline illumination port](#). For applications that do not require ethernet controlled functionality, [Advanced Illumination High Intensity In-Line Lights](#) are also available.

Note: 24V power supply ([#66-855](#)) and DCS-100E Single Output Controller ([#18-645](#)) are required for use.