

TECHSPEC[®] 38.1mm Dia., 9.53mm Thick, Laser Mirror Substrate



TECHSPEC[®] Laser Mirror Substrates

Stock **#23-898** **3 In Stock**

-

1

+

£96⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-5	£96.80 each
Qty 6-25	£77.60 each
Qty 26-49	£72.40 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Laser Mirror Substrate

Type:

Physical & Mechanical Properties

<3

Parallelism (arcmin):

Clear Aperture (%):

90	
Commercial Polish	Back Surface:
38.10 +0.00/-0.10	Diameter (mm):
9.53 ±0.20	Thickness (mm):
Optical Properties	
10-5	Surface Quality:
λ/10	Surface Flatness (P-V):
Uncoated	Coating:
Fused Silica (Corning 7980)	Substrate: □
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- λ/10 and λ/20 Surface Flatness and 10-5 Surface Quality
 - High Quality Fused Silica Substrates
 - Imperial Sizes with Circular or Rectangular Geometries
 - Window Substrates Also Available
- TECHSPEC® Laser Mirror Substrates are manufactured from high quality fused silica and are designed for use with high power laser sources. These mirrors feature excellent surface specifications, including λ/10 and λ/20 surface flatness and 10-5 surface quality, to limit the possibility of reduced performance due to surface defects. The high surface quality of these mirror blanks also makes them ideal for use in demanding intra-cavity laser applications. TECHSPEC Laser Mirror Substrates are available in standard imperial sizes, with either circular or rectangular geometries. Please contact us if your application requires a custom size laser mirror substrate.