

TECHSPEC®

25.4mm Dia. x 150.0mm FL, MgF₂ Coated, Plano-Convex Lens



Stock **#38-266** 3-4 DAYS

[Other Coating Options](#)

-

1

+

£29.75

ADD TO CART

Qty 1-9
£29.75
Qty 10+
£26.77
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):

150.00 @587.6nm
Back Focal Length BFL (mm): 148.02
Coating: MgF ₂ (400-700nm)
Coating Specification: R _{avg} ≤1.75% @ 400 - 700nm
Substrate: ☐ N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.95
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 24.4
f/#: 5.91
Numerical Aperture NA: 0.08
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 700
Damage Threshold, Reference: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant